



# SV 3073.000

## Busbar support

State: 18/04/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3073.000 - Busbar support

For busbar systems 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).



## Features

|                       |   |
|-----------------------|---|
| Model No.             | SV 3073.000   |
| Material              | Fibreglass-reinforced, thermoplastic polyester (PBT)<br>Fire protection corresponding to UL 94-V0 |
| Colour                | RAL 7035  |
| Number of poles       | 3-pole<br>100 mm  |
| To fit busbars        | 30 x 10<br>40 x 10<br>50 x 10<br>60 x 10  |
| Rated current max.    | 1,250 A   |
| Dimensions            | Width: 22 mm<br>Height: 320 mm<br>Depth: 70 mm  |
| Packs of              | 4 pc(s).  |
| Net weight            | 1.612 kg  |
| Gross weight          | 1.83 kg   |
| Customs tariff number | 85469010  |
| ETIM 9                | EC001166  |
| ETIM 8                | EC001166  |

# Features

---

ECLASS 8.0

27400607

---

Product description

SV Busbar support, 3-pole, 100 mm bar centre distance, for busbar  
WH: 30-60x10 mm

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK

# Tender text

SV busbar support

for accommodating busbars. 3-pole busbar support  
with 100 mm bar centre distance.

Rated operating voltage: 1000 V~, 50/60 Hz  
to VDE 0660

Rated current: up to 1250 A

Material: PBT

Fire protection: UL 94-V0

Continuous operating temperature: 140 °C

Bar centre distance: 100 mm

Bar accommodation without inserts: 60 x 10 mm

Tightening torques

Assembly screws: 8 - 10 Nm

Lid attachment: 1 - 3 Nm

Approvals:

DNV, GL, VDE, ÖVE, SEV, KEMA