

Rittal – The System.

Faster – better – everywhere.



SK 3322.700 Chopped-fibre filter mat

State: 28/06/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3322.700 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

| | |
|-----------------------|--|
| Model No. | SK 3322.700 |
| Design | for filter fans |
| Product description | Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material | Chemical fibres |
| Note | No suitable for use in EMC filter fans. |
| To fit Model No. | 3238.... |
| Dimensions | Width: 120 mm Height: 120 mm Depth: 11 mm |
| Filter class | to DIN EN 779: G2 to DIN EN ISO 16890: ISO Coarse 50% |
| Packs of | 5 pc(s). |
| Net weight | 0.01 kg |
| Gross weight | 0.013 kg |
| Customs tariff number | 56039390 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |
| Product description | SK Spare filter mat, for fan-and-filter units, for SK 3238.... WxHxD: 120 x 120 x 11 mm |

Approvals

Approvals

CSA

UR + C-UR (recognized)