

Rittal – The System.

Faster – better – everywhere.



SK 3322.720

Pleated filter

State: 9/02/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3322.720 - Pleated filter for fan-and-filter units, roof-mounted fans, cooling units and chillers

The high-quality pleated filter technology permits a significant increase in the volumetric air flow compared to conventional chopped-fibre filter mats. Cooling unit performance is improved and energy consumption is lower. The enhanced filtration properties also mean less dust in the enclosure or unit, and the resulting longer maintenance intervals reduce service costs significantly.



Features

| | |
|--------------------------------------|---|
| Model No. | SK 3322.720 |
| Design | for filter fans / outlet filters |
| Material | PET |
| Colour | White |
| Note | Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats. |
| To fit Model No. | 3238.xxx |
| Dimensions | Width: 114 mm Height: 114 mm Depth: 14 mm |
| Filter class | to DIN EN 779: G4 to DIN EN ISO 16890: ISO Coarse 70% |
| IP protection category to IEC 60 529 | IP 54 in fan-and-filter units/roof-mounted fans/outlet filters |
| Note on Model No. | No suitable for use in EMC filter fans. |

Features

| | |
|-----------------------|---------------|
| Packs of | 5 pc(s). |
| Net weight | 0.095 |
| Gross weight | 0.1 |
| Customs tariff number | 56039390 |
| EAN | 4028177969162 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |

Approvals

| | |
|-----------|------------------------|
| Approvals | UR + C-UR (recognized) |
|-----------|------------------------|