

Rittal – The System.

Faster – better – everywhere.



SK 3351.230

Vario rack-mounted fans for 482.6 mm (19")

State: 4/06/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3351.230 - Vario rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480 m³/h

Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots. Guide frame ensures easy maintenance of the fan.

Features

| | |
|-------------------------------------|--|
| Model No. | SK 3351.230 |
| Product description | Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots. |
| Benefits | Guide frame ensures easy maintenance and replacement of the fans |
| Colour | RAL 7035 |
| Supply includes | Fully wired unit ready for connection Terminal strip and assembly parts |
| Air throughput (unimpeded air flow) | 480 m ³ /h |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Rated current max. | At 50 Hz: 0.36 A At 60 Hz: 0.33 A |
| Pre-fuse | Miniature circuit-breaker/fuse: 6 A |
| Dimensions | Width: 482.6 mm Height: 44 mm Depth: 200 mm |
| Distance between axes of fans | 85 mm |
| No. of fans | 3 |
| Noise level | At 50 Hz: 51 dB(A) |
| Operating temperature range | -10 °C...55 °C |
| Packs of | 1 pc(s). |

Features

| | |
|-----------------------|---|
| Net weight | 2.5 kg |
| Gross weight | 2.712 kg |
| Customs tariff number | 84145915 |
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Product description | SK rack-mounted fan, for 482.6 mm (19"), 480 m ³ /h, 230 V, 1~, 50/60 Hz, WHD: 482.6 x 44 x 200 mm |

Approvals

| | |
|--------------|-------------------------------|
| Approvals | UR + C-UR (recognized) VDE |
| Explanations | Declaration of conformity |
