


Rittal – The System.

Faster – better – everywhere.



HD 4000.240 Levelling feet HD

State: 13/07/2025 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.240 - Levelling feet HD

Levelling feet HD minimise cleaning time thanks to fully covered, permanently sealed threads and provide compensation of floor inclines up to an angle of 10° thanks to flexible base plate.

Features

Model No.	HD 4000.240
Design	without base mount
Benefits	Minimises cleaning time thanks to fully covered, permanently sealed threads Compensation of floor inclines up to an angle of 10° thanks to flexible base Baying can even be achieved on sloping floors, thanks to a large levelling range Certification to 3-A Sanitary Standards
Material	Stainless steel 1.4301 (AISI 304)
Supply includes	Assembly parts and seals
Load capacity	Max. 7000 N static per levelling foot
Dimensions	Thread: M12
To fit	Enclosure type: HD compact enclosure VX VX SE TS
Levelling range	122 - 175 mm
Packs of	4 pc(s).
Net weight	2
Gross weight	2.342
Customs tariff number	73181900
EAN	4028177707641
ETIM 9	EC002622
ETIM 8	EC002622

Features

ECLASS 8.0

27189263