
## Rittal – The System.

Faster - better - everywhere.





# AS 4050.736 Wire end ferrules

State: 18/11/2025 (Source: rittal.com/au-en)



## AS 4050.736 - Wire end ferrules loose

With plastic collar.

#### **Features**

Model No.	AS 4050.736
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Yellow
Length	12 mm
AWG	10
Internal diameter	6.3 mm
For cross-section	6 mm²
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Standards	AEH DIN 46228
To fit Model No.	4051.210
Delivery form	Loose
Packs of	100 pc(s).
Net weight	0.1
Gross weight	0.1
Customs tariff number	85369010
EAN	4028177805040
ETIM 9	EC000005

© Rittal 2025 2

## Features

ETIM 8	EC000005
ECLASS 8.0	36659290

# **Approvals**

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3