

**Rittal – The System.**

Faster – better – everywhere.



# AS 4050.736

## Wire end ferrules

State: 7/04/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.736 - Wire end ferrules loose

With plastic collar.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | AS 4050.736   |
| Product description      | With plastic collar.  |
| Technical specifications | Heat-resistant to 105 °C  |
| Material                 | E-Cu, galvanic tin-plated<br>Plastic collar: Polypropylene  |
| Colour                   | Yellow  |
| Length                   | 12 mm   |
| AWG                      | 10  |
| Internal diameter        | 6.3 mm  |
| For cross-section        | 6 mm <sup>2</sup>   |
| DIN colour code          | Yes   |
| Note                     | UL-certified in conjunction with the relevant tools, such as crimping machines.<br>For bespoke advice, please contact your Rittal sales consultant. |
| Standards                | AEH DIN 46228   |
| To fit Model No.         | 4051.210  |
| Delivery form            | Loose   |
| Packs of                 | 100 pc(s).  |
| Net weight               | 0.1 kg  |
| Gross weight             | 0.1 kg  |
| Customs tariff number    | 85369010  |
| ETIM 9                   | EC000005  |
| ETIM 8                   | EC000005  |

# Features

---

|                     |   |
|---------------------|---|
| ECLASS 8.0          | 36659290  |
| Product description | Wire end ferrules for wire processing, 6 mm <sup>2</sup> , yellow, loose, 12 mm |

---

# Approvals

---

|           |                          |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed)<br>UR |
|-----------|--------------------------|