


Rittal – The System.

Faster – better – everywhere.



AS 4050.740 Wire end ferrules

State: 2/08/2025 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.740 - Wire end ferrules loose

With plastic collar.



Features

| | |
|--------------------------|---|
| Model No. | AS 4050.740 |
| Product description | With plastic collar. |
| Technical specifications | Heat-resistant to 105 °C |
| Material | E-Cu, galvanic tin-plated Plastic collar: Polypropylene |
| Colour | Black |
| Length | 12 mm |
| AWG | 16 |
| Internal diameter | 3.5 mm |
| For cross-section | 1.5 mm ² |
| DIN colour code | Yes |
| Note | UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant. |
| Standards | AEH DIN 46228 |
| To fit Model No. | 4051.205 4051.210 |
| Delivery form | Loose (10 packs of 100) |
| Packs of | 1,000 pc(s). |

Features

| | |
|-----------------------|---------------|
| Net weight | 1 |
| Customs tariff number | 85369010 |
| EAN | 4028177805088 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |

Approvals

| | |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed) UR |
|-----------|--------------------------|