


# Rittal – The System.

Faster – better – everywhere.



## AS 4051.105 LED work light

State: 12/05/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.105 - LED work light for WS 540

For attaching to the table top, with clamping device.



## Features

Model No.	AS 4051.105
Product description	For attaching to the table top, with clamping device.
Benefits	<p>Bright, glare- and flicker-free lighting, homogeneous and shadow-free</p> <p>Selectable colour temperature between warm white, neutral white and daylight white promotes concentration and reduces symptoms of fatigue</p> <p>Excellent colour fidelity and high contrast</p> <p>Aluminium spring arm with 3D head joint, swivelling and lockable for free positioning of the light source</p>
Technical specifications	<p>Spring arm: Length 970 mm</p> <p>Colour reproduction: 94 – 98 Ra</p> <p>Transmission angle: 100°</p>
Material	<p>Light housing: Aluminium</p> <p>Glare control: Macrolon</p>
Supply includes	<p>LED work light</p> <p>Assembly parts</p>
Power consumption	26 W
Length of connection cable	3 m
Connection options	Plug-in power supply (CEE 7/16) with AC adaptor
Light	84 SMD LEDs

# Features

Protection class	III (SELV)
Luminous flux	2,930 lm
To fit Model No.	4051.100
Operating temperature range	-10 °C...40 °C
Rated operating voltage	110 V - 240 V, 1~, 50 Hz/60 Hz
Dimensions	Width: 545 mm Height: 90 mm Depth: 35 mm
Packs of	1 pc(s).
Net weight	2.5 kg
Gross weight	4.2 kg
Customs tariff number	94054990
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36629090
Product description	LED work light for WS 540, dimmable, 230 V/50 Hz