

Rittal – The System.

Faster – better – everywhere.



AS 4051.605 Wire end ferrules

State: 15/05/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.605 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.605
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Blue
Length	10 mm
AWG	14
Internal diameter	4.2 mm
For cross-section	2.5 mm ²
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packs of	3,000 pc(s).
Net weight	3 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Product description	Wire end ferrules 2.5 mm ² x 10 mm AWG 14, packs of 3,000 pc(s)., colour: blue, delivery form: on belt (in accordance with the DIN/Rittal colour code)

Approvals

Approvals

UL + C-UL (listed)