

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.726 Wire end ferrules

State: 28/08/2025 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.726 - Wire end ferrules loose

With plastic collar.

## Features

Model No.	AS 4051.726
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Grey
Length	18 mm
AWG	14
Internal diameter	4.2 mm
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Standards	AEH DIN 46228
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5
Customs tariff number	85369010
EAN	4028177999961
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Approvals

---

Approvals

UL + C-UL (listed)

UR