

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.727 Wire end ferrules

State: 21/07/2025 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.727 - Wire end ferrules loose

With plastic collar.

## Features

Model No.	AS 4051.727
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Orange
Length	8 mm
AWG	12
Internal diameter	4.8 mm
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5
Customs tariff number	85369010
EAN	4028177999978
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

## Approvals

# Approvals

---

Approvals

UL + C-UL (listed)

UR