

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.008 Crimping pliers

State: 13/05/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.008 - Crimping pliers for wire end ferrules

For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.



## Features

Model No.	AS 4054.008
Design	Straight
Product description	For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.
Benefits	Minimal effort required with large wire cross-sections Uniformly high quality compression Marked die stations for precise machining of the relevant cross-sections Releasable ratchet
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	WM crimp
Direction of cable entry	Side
Dimensions	Height: 68 mm Length: 256 mm
AWG	2 - 1
For cross-section	35 - 50 mm <sup>2</sup>
Packs of	1 pc(s).

# Features

---

Net weight	0.64 kg
Gross weight	0.69 kg
Customs tariff number	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	Crimping pliers for wire end ferrules

---