


Rittal – The System.

Faster – better – everywhere.



AS 4055.180

Splitter hole punch set, metric

State: 22/08/2025 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.180 - Splitter hole punch set, metric for stainless steel, round, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.180
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	5 female dies 5 male dies Plastic case
Machinable material	Stainless steel
Maximum machinable material thickness, stainless steel	2 mm 2 mm 2 mm 2.5 mm 2.5 mm
Ø punch	16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm
For threads	M16 M20 M25 M32 M40
Note	When operating with wrenches, tension screws with ball bearings should be used.

Features

Suitable for hydraulic bolt order number	4055.665
	4055.665
	4055.665
	4055.663
	4055.663
Packs of	1 pc(s).
Net weight	0.849
Gross weight	1.098
Customs tariff number	82034000
EAN	4028177808171
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049047