

# Rittal – The System.

Faster – better – everywhere.



## AS 4055.580

## Splitter hole punch set, M16 to M40

State: 27/08/2025 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.580 - Splitter hole punch set, M16 to M40 for sheet steel, with triple splitting

For punching round cut-outs

## Features

|  |   |
|--|---|
| Model No.  | AS 4055.580   |
| Design   | With triple splitting   |
| Product description                                | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes                                    | 5 female dies<br>5 male dies<br>Plastic case  |
| Machinable material                                | Sheet steel   |
| Maximum machinable material thickness, sheet steel | 2 mm<br>2 mm<br>2 mm<br>3 mm<br>3 mm  |
| Ø punch  | 16.2 mm<br>20.4 mm<br>25.4 mm<br>32.5 mm<br>40.5 mm                                       |
| For threads  | M16<br>M20<br>M25<br>M32<br>M40   |
| Note   | When operating with wrenches, tension screws with ball bearings should be used.           |

# Features

|  |               |
|--|---------------|
| Suitable for hydraulic bolt order number | 4055.661      |
|  | 4055.661      |
|  | 4055.661      |
|  | 4055.663      |
|  | 4055.663      |
| Packs of                                 | 1 pc(s).      |
| Net weight                               | 1             |
| Gross weight                             | 1.039         |
| Customs tariff number                    | 82034000      |
| EAN                                      | 4028177808836 |
| ETIM 9                                   | EC002121      |
| ETIM 8                                   | EC002121      |
| ECLASS 8.0                               | 21044719      |