Rittal – The System.

Faster - better - everywhere.





SZ 4127.210 Door-operated switch

State: 17/11/2025 (Source: rittal.com/au-en)



SZ 4127.210 - Door-operated switch

with mounting accessories, with or without connection cable.

Features

Model No.	SZ 4127.210	
Design	with toggle for swing frame, without connection cable	
Function principle	The toggle is actuated via the tubular door frame of the sheet steel door, or in the case of glazed doors, via an adaptor included with the supply.	
Note	For installation in VX IT only in conjunction with VX mounting bracket for door-operated switch	
Rated impulse withstand voltage, phase to phase	6000 V AC	
Rated insulation voltage	400 V AC	
Installation options	for TS enclosures with installed large swing frame for standard and courtesy light	
Electrical connection	240 V AC/6 A 125 V AC/8 A 24 V AC/6 A 24 V DC/6 A	
Rated operating voltage	400 V	
IP protection category to IEC 60 529	IP 40	
Packs of	1 pc(s).	
Net weight	0.231	
Gross weight	0.235	
Customs tariff number	85365019	
EAN	4028177581326	
ETIM 9	EC002626	
ETIM 8	EC002626	

© Rittal 2025

Features

27189266
27189266

Approvals

Approvals	CQC
	CQC-CCC
	CSA
	UL + C-UL (listed)
Explanations	Declaration of conformity
•	Declaration of conformity UK

© Rittal 2025 3