Rittal – The System.

Faster – better – everywhere.



SZ 4315.520

Door-operated switch

State: 22/12/2025 (Source: rittal.com/au-en)

SZ 4315.520 - Door-operated switch

with mounting accessories, with or without connection cable.

Features

Model No.	SZ 4315.520
Design	With connection cable
Length	600 mm
Rated impulse withstand voltage, phase to phase	6000 V AC
Rated insulation voltage	400 V AC
Installation options	for standard and courtesy light without integral door-operated switch
Dimensions	Length: 600 mm
Electrical connection	240 V AC/6 A 125 V AC/8 A 24 V AC/6 A 24 V DC/6 A
Rated operating voltage	400 V
IP protection category to IEC 60 529	IP 40
Packs of	1 pc(s).
Net weight	0.119
Gross weight	0.124
Customs tariff number	85365019
EAN	4028177581357
ETIM 9	EC002626
ETIM 8	EC002626
ECLASS 8.0	27189266

© Rittal 2025

Approvals

Approvals	CQC CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK