


Rittal – The System.

Faster – better – everywhere.



VX 5301.257

Side panel, horizontally divided

State: 17/04/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.257 - Side panel, horizontally divided for VX IT

Side panels, horizontally divided, for VX IT

Features

Model No.	VX 5301.257
Product description	For sealing IT enclosure systems, both stand-alone and baying arrangements.
Benefits	Easy to use Supports tool-free installation and removal of the side wall Locked using security lock 3524 E Integral internal latch
Material	Sheet steel
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Console Pedestal 6 mounting brackets 2 lock components Assembly parts
To fit	Enclosure type: VX IT Height: = 2,200 mm Depth: = 1,000 mm
IP protection category to IEC 60529	IP 20
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	19.4 kg
Gross weight	19.8 kg
PCF per pack (cradle-to-gate)	75.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared

Features

Customs tariff number	94039910
ETIM 9	EC002524
ECLASS 8.0	27182101
Product description	Side panel, divided horizontally for VX IT for sealing IT enclosure systems in stand-alone or baying arrangement. For enclosure height 2,200 mm, for enclosure depth 1,000 mm.