

# Rittal – The System.

Faster – better – everywhere.



## DK 5301.540

## Sheet steel door, one-piece, solid

State: 17/08/2025 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5301.540 - Sheet steel door, one-piece, solid for VX IT

To replace existing doors.



## Features

Model No.	DK 5301.540
Product description	To replace existing doors.
Material	Sheet steel
Surface finish	Spray-finished
Colour	Door: RAL 7035 Comfort handle VX: RAL 9005
Supply includes	Door with comfort handle for semi-cylinders with security lock 3524 E 4 x 130° hinges, inside Assembly parts
Assembly instruction	For a door opening angle of 180° when baying, a 180° baying hinge is required
Note	Door opening angle for stand-alone siting: max. 165° Door opening angle when baying: max. 110°
IP protection category to IEC 60529	IP 55

# Features

To fit	Enclosure type: VX IT Width: = 800 mm Height: = 2,000 mm
Packs of	1 pc(s).
Net weight	31.6
Gross weight	32.6
PCF per pack (cradle-to-gate)	124.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177955080
ETIM 9	EC000747
ECLASS 8.0	27182204