

Rittal – The System.

Faster – better – everywhere.



DK 5302.046 Cable finger

State: 12/03/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.046 - Cable finger for VX IT

For U-based cable routing.

Features

Model No.	DK 5302.046
Design	for VX IT 482.6 mm (19") mounting angles, dynamic
Product description	For structured cable routing on the 482.6 mm (19") mounting level in 1 U increments.
Benefits	Simple, tool-free installation by snap-mounting directly into the 482.6 mm (19") mounting angle
Material	Plastic to UL 94-V0 Plastic PA6, halogen-free
Colour	RAL 9005
Installation options	Installation is possible both on the front and on the side of the mounting angles at the front and rear
Note	Cable routing in conjunction with air baffle plates is supported
Dimensions	Width: 25 mm Length: 261 mm
Units	6 U
Packs of	14 pc(s).
Net weight	1.652 kg
Gross weight	1.677 kg
Customs tariff number	39269097
ETIM 9	EC000322
ECLASS 8.0	27400703
Product description	Cable finger, 6 U, for VX IT 19" mounting angles, dynamic, for structured cable routing on the 19" mounting level in 1 U increments. Plastic in accordance with UL 94-V0