

# Rittal – The System.

Faster – better – everywhere.



## DK 5501.815

## Air baffle plates for TS IT 482.6 mm (19") mounting angles

State: 31/07/2025 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.815 - Air baffle plates for TS IT 482.6 mm (19") mounting angles

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



## Features

|                      |  |
|----------------------|--|
| Model No.            | DK 5501.815  |
| Product description  | With all-round brush strip for collision-free shielding with installed bar systems on the outer mounting level.  |
| Applications         | To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.   |
| Material             | Sheet steel<br>Blanking panel: Plastic, UL 94-HB, halogen-free<br>Brush strip: Plastic, UL 94-HB   |
| Surface finish       | Spray-finished   |
| Colour               | RAL 9005   |
| Supply includes      | 2 vertical trim panels<br>2 horizontal trim panels<br>4 brush strips<br>4 cellular PU foam pieces<br>Assembly parts<br>6 blanking panels, 1 U  |
| Assembly instruction | The vertical trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting angles for partitioning.<br>The horizontal trim panels with brush strips can only be mounted on the front 482.6 mm (19") mounting angles. |

# Features

|                       |                                   |
|-----------------------|-----------------------------------|
| To fit                | Width: 800 mm<br>Height: 2,000 mm |
| Packs of              | 1 pc(s).                          |
| Net weight            | 7.679                             |
| Gross weight          | 8.02                              |
| Customs tariff number | 73269098                          |
| EAN                   | 4028177679184                     |
| E-Number Sweden       | E7239699                          |
| ETIM 9                | EC000331                          |
| ECLASS 8.0            | 27189272                          |

# Tender text

## Air baffle plate

Air baffle plate to separate hot/cold zones within an enclosure or complete enclosure suites.

An all-round brush strip ensures collision-free shielding with installed bar systems on the outer mounting level.

Tool-less mounting on the mounting angles of the 482.6 mm (19") level via quick-action fastener or screw-fastened as an option.

May be used, for example for Rittal enclosure series TS IT.

For enclosure (WxH) 800x2000 mm.

Integral mounting holes for optional accommodation of up to 3x1 U components in 482.6 mm (19") width format per side.

Trims pre-configured with 482.6 mm blanking panels, made from plastic, tool-less assembly

Material: Air baffle plates, sheet steel,  
Brush strips and 482.6 mm (19") blanking  
Plastic UL 94- HB

Model No. DK: 5501.815

Manufacturer: Rittal