

# Rittal – The System.

Faster – better – everywhere.



## DK 5501.885

# Air baffle plates for TS IT 482.6 mm (19") mounting frames

State: 4/04/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.885 - Air baffle plates for TS IT 482.6 mm (19") mounting frames

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



## Features

Model No.	DK 5501.885
Product description	With all-round brush strip for collision-free shielding with installed rail systems on the outer mounting level.
Applications	To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.
Material	Sheet steel Blanking panel: Plastic, UL 94-HB, halogen-free Brush strip: Plastic, UL 94-HB
Surface finish	Spray-finished
Colour	RAL 9005
Supply includes	2 vertical trim panels 2 horizontal trim panels 4 brush strips Assembly parts 2 blanking panels, 3 U
Assembly instruction	The vertical and horizontal trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting frame for partitioning.

# Features

To fit	Width: 800 mm Height: 1,800 mm
Packs of	1 pc(s).
Net weight	5.5 kg
Gross weight	6 kg
Customs tariff number	73269098
ETIM 9	EC000331
ECLASS 8.0	27189272
Product description	DK Air baffle plate, WxH: 800x1800 mm, For TS IT 482.6 mm (19") mounting frames