

# Rittal – The System.

Faster – better – everywhere.



## CP 6532.200

# Command panel based on AE, with handle strips

State: 18/04/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6532.200 - Command panel based on AE, with handle strips

Sheet steel enclosure with triple surface treatment provides optimum protection against corrosion. Aluminium front panel, easily dismantled for machining. Fast and safe servicing access from the front and rear.

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | CP 6532.200   |
| Material                            | Enclosure and door: Sheet steel<br>Handle strips: Aluminium<br>Cover caps: Plastic  |
| Surface finish                      | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Handle strips: Powder-coated  |
| Colour                              | Enclosure and door: RAL 7035<br>Handle strips and cover caps: RAL 7030  |
| Supply includes                     | Enclosure with cut-out and reinforcement for support arm system CP-L, Ø 130 mm<br>Mounting angles spot welded at the sides<br>Front with maximum cut-out, covered with easily machinable 3 mm aluminium front panel<br>Side handle strips with cover caps<br>Rear door with r/h hinge<br>Cam lock with 3 mm double-bit insert |
| Dimensions                          | Width: 500 mm<br>Height: 500 mm<br>Depth: 210 mm  |
| IP protection category to IEC 60529 | IP 55   |
| Note                                | The support arm connection and door hinge may be swapped over by rotating the enclosure   |
| Basic material                      | Aluminium   |

# Features

---

|                       |           |
|-----------------------|-----------|
| Packs of              | 1 pc(s).  |
| Net weight            | 13.786 kg |
| Gross weight          | 14.512 kg |
| Customs tariff number | 94032080  |
| ECLASS 8.0            | 27180505  |

# Approvals

---

|           |    |
|-----------|----|
| Approvals | UL |
|-----------|----|