## Rittal – The System.

Faster – better – everywhere.





# TP 6742.600 One-piece consoles TP

State: 8/12/2025 (Source: rittal.com/au-en)



## TP 6742.600 - One-piece consoles TP

One-piece console for operating and monitoring, with large mounting plate and a high protection category of IP 55, available in four different widths. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

#### **Features**

TD (740 (00
TP 6742.600
Enclosure: Sheet steel 1.5 mm  Door and console cover: Sheet steel, 2.0 mm, all-round foamed-in PU seal  Mounting plate: Sheet steel, 3.0 mm
Enclosure, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
RAL 7035
Enclosure, solid back and sides Door or double door at front, with locking rod Mounting plate Cover hinged at rear, 2 stays with automatic locking. Automatic unlocking on the left, manual unlocking on the right Gland plates
Width: 1,200 mm Height: 975 mm Depth: 400 mm
1,130 mm x 900 mm
500 mm
400 mm
2
IK08
Positioning slide VX 5051.172 can be used as a mounting aid for base/plinth system VX in its new design

© Rittal 2025 2

## **Features**

IP protection category to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Basic material	Sheet steel
Dimensions	Width: 1,200 mm Height: 975 mm Depth (top): 500 mm Depth (bottom): 400 mm
Packs of	1 pc(s).
Net weight	90
Gross weight	93.5
Customs tariff number	94032080
EAN	4028177959958
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

## **Approvals**

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3