

Rittal – The System.

Faster – better – everywhere.



DK 7072.230

Nylon loop

State: 8/07/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7072.230 - Nylon loop

With the nylon loop, secured cables are easily released, allowing individual cables to be added or removed, ideal for sensitive data cables (fibre-optic/Cu).

Features

Model No.	DK 7072.230
Product description	With the nylon loop, secured cables are easily released, allowing individual cables to be added or removed. Ideal for sensitive data cables (fibre-optic/Cu), as it avoids indentations on the cable sheathing. In addition, the nylon loop may be screw-fastened to the round system punchings or attached using a quick-release fastener.
Colour	Black
Supply includes	Quick-release fastener
Dimensions	Width: 20 mm Length: 200 mm
Max. cable diameter	50 mm
Packs of	10 pc(s).
Net weight	0.03 kg
Gross weight	0.041 kg
Customs tariff number	58061000
ETIM 9	EC002625
ECLASS 8.0	27189234
Product description	DK Nylon loop, WxL: 20x200 mm, For Ø: 50 mm

Tender text

Nylon loop for cable routing, max. cable diameter 50 mm

The nylon loop is attached to cable clamp rails, C rails, system rails or to the enclosure frame. The nylon loop may be screw-fastened as per the 25 mm DIN pitch pattern. The nylon loop can hold cable bunches up to 50 mm in diameter; single cables can easily be added or detached.

Nylon loop length: 200 mm

Max. cable diameter: 50 mm