

Rittal – The System.

Faster – better – everywhere.



DK 7320.793 Door switch

State: 23/05/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7320.793 - Door switch

Switch for connecting to the normally closed contacts of the door control module for manual door opening.

Features

| | |
|-----------------------|---|
| Model No. | DK 7320.793 |
| Product description | Switch for connecting to the normally closed contacts of the door control module for manual door opening. For mounting on the 25 mm pitch pattern of the TS IT frame section. |
| Supply includes | 3 m connection cable Mounting bracket Assembly parts |
| Installation Ø | 16.2 mm |
| Rated voltage | 250 V AC |
| Rated current (max.) | 2 A |
| Packs of | 1 pc(s). |
| Net weight | 0.17 kg |
| Gross weight | 0.178 kg |
| Customs tariff number | 85311095 |
| ETIM 9 | EC001770 |
| ECLASS 8.0 | 27390190 |
| Product description | DK Door switch, 250 V AC, 2 A, Einbau-Ø: 16,2 mm |

Approvals

| | |
|--------------|-----|
| Certificates | EAC |
|--------------|-----|

Tender text

7320.793

Door switch

Button with integrated switching contact as opener. The system can be used in connection with the CMC III Door Control Module. The interruption of the contact when the button is pressed is recognised by the CMC III Door Control Module, and the solenoids are de-energised so that the door of a rack can be released and/or opened. For mounting in the LCP.

Technical specifications:

Rated voltage: 250 V AC

Rated current: max. 2 A