

# Rittal – The System.

Faster – better – everywhere.



## DK 7824.086 Side panel, lockable

State: 5/06/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7824.086 - Side panel, lockable for TS, TS IT

Side panel, lockable, sheet steel, for TS.

## Features

Model No.	DK 7824.086
Product description	Simply locate from above. Lock with security lock no. 3524 E. Earthing bolt with contact track.
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 7035
Supply includes	2 side panels each with 4 security locks no. 3524 E
To fit	Enclosure type: TS TS IT Height: 800 mm Depth: 600 mm
Basic material	Sheet steel
Packs of	2 pc(s).
Net weight	11.4 kg
Gross weight	12.4 kg
Customs tariff number	94039910
ETIM 9	EC002524
ECLASS 8.0	27182101
Product description	DK Side panel, WxH: 800x1200 mm, HxD: 800x600 mm, RAL 7035

# Tender text

Side panel, plug-type for DK-TS

Lockable side panel with 2 options:

Lockable by exchanging the lock for cam locks with security inserts no. 3524 E.

Additional security is achieved via the option of securing the side panel from inside. The side panels on the frame section are screw-fastened from the inside with securing brackets. The side panel can only be opened in case of access via the front door.

The security standard corresponds to that of the semi-cylinder fitted in the front door.

Plug-and-play attachment via simple plugging-in, closing and locking. The 25 mm pitch pattern of holes integrated within the vertical top hat rail offers additional attachment options for installation or cable routing components.

Material: 1.5 mm sheet steel

Surface finish: RAL 7035

For enclosure dimensions: H: 800 mm D: 600