

# Rittal – The System.

Faster – better – everywhere.



## DK 7828.040 C rails

State: 6/06/2025 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7828.040 - C rails for TS, VX SE

For direct external mounting between the vertical TS, SE enclosure sections. The C-section angle bracket is additionally required for mounting between the horizontal TS, SE enclosure sections. Thanks to the universal attachment piece, the C rails may be optionally attached to the inner or outer level of the TS 8 frame.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | DK 7828.040   |
| Product description   | For direct external mounting between the vertical TS, SE enclosure sections. The angle bracket, C-section, is additionally required for mounting between the horizontal TS, SE enclosure sections. The universal design of the attachment piece allows the C rails to be optionally attached to the inner or outer level of the TS 8 frame. |
| Material              | Sheet steel   |
| Surface finish        | Zinc-plated   |
| Supply includes       | Assembly parts  |
| Length                | 298 mm  |
| To fit                | Enclosure type: TS<br>SE<br>Width: = 400 mm<br>Depth: = 400 mm  |
| Packs of              | 4 pc(s).  |
| Net weight            | 1.2   |
| Gross weight          | 1.332   |
| Customs tariff number | 73269098  |
| EAN                   | 4028177235038   |
| ETIM 9                | EC000386  |
| ECLASS 8.0            | 27400501  |

# Tender text

C rail for TS 8

Type of attachment: in the enclosure depth

Distance between 19" levels: 445/495 mm

Material: Sheet steel, zinc-plated, passivated

for enclosure dimensions: W: 400 mm D: 400 mm