

Rittal – The System.

Faster – better – everywhere.



TE 7888.653

Side panel

State: 5/06/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7888.653 - Side panel for TE 8000

Side panels, for TE 8000.

Features

Model No.	TE 7888.653
Product description	Simple assembly with insertion aid at the bottom and lock at the top. Earthing bolt with contact lug.
Material	Sheet steel
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	4 cam locks including security lock 3524 E
To fit	Enclosure type: TE 8000 Height: 2,000 mm Depth: 1,000 mm
IP protection category to IEC 60529	IP 20
Basic material	Sheet steel
Packs of	2 pc(s).
Net weight	25 kg
Gross weight	29.5 kg
Customs tariff number	94039910
ETIM 9	EC002524
ECLASS 8.0	27182101
Product description	TE Side panel, HxD: 2000x1000 mm, For TE 8000

Tender text

TE 8000 side panel, lockable

Item TE 7888.653

One-part, plug-in side panel with security lock no. 3524 E.

Quick fastening is achieved by simply plugging-in, closing and locking.

Supply includes: 2 side panels each with 2 security locks

Material: Sheet steel

Surface finish: RAL 7035

Approvals: ---

For enclosure dimensions (WxH): 1000 x 2000 mm

Protection category: IP 20, bayed

Model No: TE 7888.653

Manufacturer: Rittal GmbH & Co. KG