

Rittal – The System.

Faster – better – everywhere.



TE 7888.944 Distributor racks

State: 24/08/2025 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7888.944 - Distributor racks TE 8000 open

For optimum accessibility from all sides during assembly and installation.

Features

Model No.	TE 7888.944
Benefits	Optimum accessibility from all sides during assembly and installation Unrestricted airflow, due to the open design The distance between attachment levels is infinitely variable
Material	Sheet steel
Surface finish	Powder-coated
General colour	RAL 7035
Colour	RAL 7035
Supply includes	Self-supporting mounting frame, with 482.6 mm (19") mounting level front and rear Roof-plate, prepared for accommodating cable organisers Open base frame with 2 punched sections with mounting flanges for individual configuration fitted in the width 4 levelling feet, M10 (supplied loose) Roof plate with brush strip on both sides
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 1,000 mm
Units	42 U
Units	42 U
Free mounting space to the 482.6 mm (19") level, front/rear	80 mm / 130 mm
Distance between levels as delivered	745 mm
Load capacity	7,000 N
Basic material	Sheet steel

Features

Packs of	1 pc(s).
Net weight	55
Gross weight	59.5
EAN	4028177801332
E-Number Sweden	E7282510
ETIM 9	EC002507
ECLASS 8.0	27180602

Tender text

TE 8000 network distributor, open frame
Item TE 7888.944

Screw-fastened, dismountable enclosure design based on two self-supporting 482.6 mm (19") mounting angles, which simultaneously form the supporting distributor frame. Roof and modular base frames connected together using 482.6 mm (19") mounting frames to form a supporting frame. Open distributor frame, without side panels and doors. Open roof frame for cable entry including three cable routing trays. Base frame with maximum cut-out for optional population with modular panels, pre-configured, with 2 punched sections in the width for individual configuration. Two depth-adjustable 482.6 mm (19") mounting frames with integrated 25 mm system punching are used for the internal assembly. Mounting frames may be secured infinitely by means of slot attachment. 350 kg load capacity per frame, max. 700 kg for each distributor. The distributor frames are bayable.

Supply includes: Open frame with levelling feet to compensate for floor irregularities.

Material: Sheet steel

Surface finish: RAL 7035

Approvals: ---

Dimensions (WHD): 800 x 2000 x 1000 mm

Installation clearance height: 42 U

Protection category: ---

Model No: TE 7888.944

Manufacturer: Rittal GmbH & Co. KG