


# Rittal – The System.

Faster – better – everywhere.



## VX 8106.245

## Side panel, screw-fastened, sheet steel

State: 22/08/2025 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8106.245 - Side panel, screw-fastened, sheet steel for VX

Side panels, screw-fastened, sheet steel, for VX.

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | VX 8106.245   |
| Benefits                            | Time-saving assembly thanks to clip-in side panel holder<br>Automatic potential equalisation and higher EMC protection, thanks to enclosure panel holders with earthing inserts located on the inside<br>Easy positioning in the height and depth with the location aid<br>One-person assembly<br>Earthing bolts with large, paint-free contact surface for optimum contact |
| Material                            | Sheet steel, 1.5 mm   |
| Surface finish                      | Dipcoat-primed, powder-coated on the outside  |
| Colour                              | RAL 7035  |
| Supply includes                     | Assembly parts  |
| To fit                              | Enclosure type: VX<br>Height: = 2,000 mm<br>Depth: = 600 mm   |
| IP protection category to IEC 60529 | IP 55<br>IP 66  |
| Type rating to UL 50E               | Type 1<br>Type 3R<br>Type 4<br>Type 12  |
| Basic material                      | Sheet steel   |
| Packs of                            | 2 pc(s).  |
| Net weight                          | 26  |
| Gross weight                        | 29  |

# Features

|                               |  |
|-------------------------------|--|
| PCF per pack (cradle-to-gate) | 110.5 kg CO2 eq (Cat B)  |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 94039910   |
| EAN                           | 4028177827417  |
| E-Number Sweden               | E3465116   |
| ETIM 9                        | EC002524   |
| ECLASS 8.0                    | 27182101   |

# Approvals

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|