


# Rittal – The System.

Faster – better – everywhere.



## TS 8610.805 Glazed door

State: 6/09/2025 (Source: [rittal.com/au-en](https://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8610.805 - Glazed door for TS, TS IT, VX SE

Instead of a sheet steel door or rear panel.



## Features

|                       |   |
|-----------------------|---|
| Model No.             | TS 8610.805   |
| Product description   | Instead of a sheet steel door or rear panel.  |
| Material              | Frame: Extruded aluminium section<br>Corner pieces: Die-cast zinc<br>Viewing window: Single-pane safety glass, 3 mm |
| Surface finish        | Powder-coated   |
| Colour                | Frame: RAL 7035<br>Corner pieces: RAL 7035<br>Viewing window (printed mask on the inside): RAL 9005                 |
| Supply includes       | Viewing door frame with safety glass<br>Locking rod with double-bit insert<br>180° hinges (4)                       |
| Visible area          | Viewing window width: 660 mm<br>Viewing window height: 1,840 mm   |
| Viewing window height | 1,840 mm  |

# Features

|                                     |   |
|-------------------------------------|---|
| Assembly instruction                | Lock components are required when mounting instead of the rear panel          |
| IP protection category to IEC 60529 | IP 55   |
| To fit                              | Enclosure type: TS<br>TS IT<br>VX SE<br>Width: = 800 mm<br>Height: = 2,000 mm |
| Packs of                            | 1 pc(s).  |
| Net weight                          | 16  |
| Gross weight                        | 17  |
| Customs tariff number               | 94039910  |
| EAN                                 | 4028177693852   |
| ETIM 9                              | EC000747  |
| ECLASS 8.0                          | 27182204  |