


Rittal – The System.

Faster – better – everywhere.



TS 8612.560

TS punched section with mounting flange, 23 x 73 mm



State: 31/01/2026 (Source: rittal.com/au-en)



FRIEDHELM LOH GROUP

TS 8612.560 - TS punched section with mounting flange, 23 x 73 mm

The alternative to the TS punched section with mounting flange 17 x 73 mm, with punchings for captive nuts/threaded blocks instead of the slotted holes top and bottom. Simply locate and secure.



Features

Model No.	TS 8612.560
Product description	The alternative to the TS punched section with mounting flange 17 x 73 mm, with punchings for captive nuts/threaded blocks instead of the slotted holes top and bottom. Simply locate and secure.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Installation options	On the vertical TS, VX SE enclosure section
To fit	Enclosure type: the inner mounting level Width/depth: 600 mm
Packs of	4 pc(s).
Net weight	2.544
Gross weight	2.74
Customs tariff number	73269098
EAN	4028177237391
ETIM 9	EC002625

Features

ECLASS 8.0

27189234