

**Rittal – The System.**

Faster – better – everywhere.



**TS 8612.680**

**TS punched sections without  
mounting flanges, 45 x 88 mm**

State: 21/06/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8612.680 - TS punched sections without mounting flanges, 45 x 88 mm

Heavy top-mounted equipment mounted directly on the internal surfaces (e.g. roof) is supported. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine.



## Features

|                       |   |
|-----------------------|---|
| Model No.             | TS 8612.680   |
| Design                | for the inner mounting level  |
| Product description   | Heavy top-mounted equipment mounted directly on the internal surfaces (e.g. roof) is supported. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine. The twin profile with 11 rows of holes offers numerous additional opportunities for interior installation. |
| Material              | Sheet steel   |
| Surface finish        | Zinc-plated   |
| Supply includes       | Assembly parts  |
| Installation options  | On the vertical and horizontal TS, VX SE enclosure section  |
| To fit                | Enclosure type: the inner mounting level<br>Width/depth: 800 mm   |
| Packs of              | 2 pc(s).  |
| Net weight            | 3.638 kg  |
| Gross weight          | 3.837 kg  |
| Customs tariff number | 73269098  |

# Features

---

|                     |   |
|---------------------|---|
| ETIM 9              | EC002625  |
| ECLASS 8.0          | 27189234  |
| Product description | TS TS punched section without mounting flange, 45 x 88 mm, for inner mounting level: for WD: 800 mm |

---