

Rittal – The System.

Faster – better – everywhere.



VX 8617.000

**Punched section with mounting
flange, 18 x 64 mm**

State: 8/07/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8617.000 - Punched section with mounting flange, 18 x 64 mm for VX

For variable, individual interior installation of the enclosure frame on the outer mounting level.



Features

Model No.	VX 8617.000
Product description	For variable, individual interior installation of the enclosure frame on the outer mounting level.
Benefits	Simply locate into the system punchings from the outside and screw-fasten System punchings on all four sides With pre-bayed enclosures, the punched sections with mounting flanges may also be fitted from the inside of the enclosure
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Installation options	On the outer mounting level, on the enclosure section On the outer mounting level, between two punched sections with mounting flanges 23 x 64 mm
To fit	Enclosure type: VX Width/depth: 300 mm
Packs of	4 pc(s).

Features

Net weight	0.88 kg
Gross weight	1.152 kg
PCF per pack (cradle-to-gate)	5.29
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189234
Product description	VX Punched section, with mounting flange 18 x 64 mm, for outer mounting level

Approvals

Explanations	PCF-declaration
--------------	-----------------