



Rittal – The System.

Faster – better – everywhere.



VX 8640.031

Base/plinth trim panels, side, 100 mm

State: 11/02/2026 (Source: [ittal.com/au-en](https://www.ittal.com/au-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 8640.031 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, sheet steel

To finish off a base/plinth unit at the sides and for additional stability, or for the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

Features

| | |
|-----------------------|--|
| Model No. | VX 8640.031 |
| Product description | To finish off a base/plinth unit at the sides and for additional stability, or for the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths. |
| Material | Sheet steel |
| Colour | RAL 9005 |
| Supply includes | Assembly parts |
| Dimensions | Height: 100 mm |
| To fit | Depth: = 400 mm |
| Type rating to UL 50E | Type 1, 12 |
| Weight/pack | 0.98 kg |
| Packs of | 2 pc(s). |
| Net weight | 0.9 |
| Gross weight | 0.96 |
| Customs tariff number | 94039910 |
| EAN | 4028177958937 |
| E-Number Sweden | E3465377 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |

Approvals

Approvals

UL + C-UL - FTTA