

# Rittal – The System.

Faster – better – everywhere.



SV 9340.260  
OM supports

State: 2/02/2026 (Source: [ittal.com/au-en](http://ittal.com/au-en))



# SV 9340.260 - OM supports without contact system

For mounting of switchgear with external power supply.

## Features

Model No.	SV 9340.260
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
For bar systems with centre-to-centre spacing	60 mm
Support rail type	Support frame, PinBlock
Number of poles	3-pole
PinBlock	Yes
Dimensions	Width: 45 mm Height: 208 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 170 mm
Approvals	UL
Packs of	1 pc(s).
Net weight	0.219
Gross weight	0.22
Customs tariff number	85369095
EAN	4028177504363
ETIM 9	EC001166
ECLASS 8.0	27400607

# Approvals

---

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

## Tender text

OM support (without contact system)  
OM support without contact system (3-pole)  
for busbar thickness 5/10 mm and PLS 800/1600  
Technical specifications  
Construction width: 55 mm  
Length: 208 mm  
Support frame: 45 x 170 mm  
Support frame support: -  
PinBlock: yes  
System:  
Rittal RiLine60