## Rittal - The System.

Faster – better – everywhere.





# SV 9345.724 Circuit-breaker component adaptor

State: 18/11/2025 (Source: rittal.com/au-en)



# SV 9345.724 - Circuit-breaker component adaptor 4-pole

#### **Features**

Model No.	SV 9345.724
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Supply includes	Copper spacer roll Connection screws
Rated current max.	500 A
Rated operating voltage	690 V, 4~
Cable outlet	Bottom
For bar systems with centre-to- centre spacing	60 mm
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgean The technical data may vary for UL applications
Number of poles	4-pole
Dimensions	Width: 185 mm Height: 300 mm
To fit busbars	Height: 5, 10 mm
To fit manufacturer (model)	Eaton
To fit manufacturer (model)	Eaton (NZM3-4-XKR130)
Packs of	1 pc(s).
Net weight	3.419
Gross weight	3.542
Copper weight (kg per piece)	2.16
Customs tariff number	85369095
EAN	4028177684539

© Rittal 2025

### Features

ETIM 9	EC001531
ECLASS 8.0	27370304

# **Approvals**

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3