

Rittal – The System.

Faster – better – everywhere.



SV 9345.724

Circuit-breaker component adaptor

State: 16/07/2025 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.724 - Circuit-breaker component adaptor 4-pole

Features

| | |
|---|---|
| Model No. | SV 9345.724 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Supply includes | Copper spacer roll Connection screws |
| Rated current max. | 500 A |
| Rated operating voltage | 690 V, 4~ |
| Cable outlet | Bottom |
| For bar systems with centre-to-centre spacing | 60 mm |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications |
| Number of poles | 4-pole |
| Dimensions | Width: 185 mm Height: 300 mm |
| To fit busbars | Height: 5, 10 mm |
| To fit manufacturer (model) | Eaton |
| To fit manufacturer (model) | Eaton (NZM3-4-XKR130) |
| Packs of | 1 pc(s). |
| Net weight | 3.419 |
| Gross weight | 3.542 |
| Copper weight (kg per piece) | 2.16 |
| Customs tariff number | 85369095 |
| EAN | 4028177684539 |

Features

| | |
|------------|----------|
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|