

Rittal – The System.

Faster – better – everywhere.



SV 9346.015 NH slimline fuse-switch disconnecter

State: 21/05/2024 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9346.015 - NH slimline fuse-switch disconnecter with electronic fuse monitoring

Features

Model No.	SV 9346.015
Material	Fibreglass-reinforced polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper
Colour	Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016
Supply includes	3 mounting hooks
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M8
Rated operating current max.	160 A
For NH size	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 50 mm Height: 400 mm
Connection for round conductor cross-sections	2.5 - 95 mm ²
To fit busbars	Height: 5, 10 mm
Rated operating voltage	690 V, 3~
Number of poles	3-pole
Packs of	1 pc(s).
Weight/pack	1.36 kg

Features

Copper weight (kg per piece)	0.73
Customs tariff number	85369095
EAN	4028177668126
ETIM 7.0	EC001046
ECLASS 8.0	27371402

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---