


# Rittal – The System.

Faster – better – everywhere.



## SV 9346.060

## NH slimline fuse-switch disconnecter

State: 16/05/2024 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9346.060 - NH slimline fuse-switch disconnecter



## Features

|                                               |                                                                                                                           |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Model No.                                     | SV 9346.060                                                                                                               |
| Material                                      | Fibreglass-reinforced polyamide<br>Fire protection corresponding to UL 94-V0<br>Contact tracks: Silver-plated hard copper |
| Colour                                        | Chassis: RAL 7035<br>Cover: RAL 7001<br>Handle: RAL 7016                                                                  |
| For bar systems with centre-to-centre spacing | 100 mm                                                                                                                    |
| Cable outlet                                  | Top/bottom                                                                                                                |
| Type of electrical connection                 | Screw M8                                                                                                                  |
| Rated operating current max.                  | 160 A                                                                                                                     |
| For NH size                                   | 00                                                                                                                        |
| Test specification                            | IEC/DIN EN 60 947-3<br>DIN EN 60 269-2 (fuse inserts)                                                                     |
| For converter installation                    | Yes                                                                                                                       |
| Dimensions                                    | Width: 50 mm<br>Height: 400 mm                                                                                            |
| Connection for round conductor cross-sections | 2.5 - 95 mm <sup>2</sup>                                                                                                  |
| To fit busbars                                | Height: 5, 10 mm                                                                                                          |

# Features

|                              |               |
|------------------------------|---------------|
| Rated operating voltage      | 690 V, 3~     |
| Number of poles              | 3-pole        |
| Packs of                     | 1 pc(s).      |
| Weight/pack                  | 1.18 kg       |
| Copper weight (kg per piece) | 0.65          |
| Customs tariff number        | 85365080      |
| EAN                          | 4028177668133 |
| ETIM 7.0                     | EC001046      |
| ECLASS 8.0                   | 27371402      |

# Approvals

|              |                                                           |
|--------------|-----------------------------------------------------------|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|-----------------------------------------------------------|