

Rittal – The System.

Faster – better – everywhere.



SV 9614.100

Mini-PLS component adaptor

State: 17/04/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9614.100 - Mini-PLS component adaptor

Maximum rated current from 12 A to 100 A.

Features

| | |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | SV 9614.100 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Connection cables (AWG) | AWG 12 |
| Rated operating voltage | 690 V, 3~ |
| Rated current max. | 25 A |
| Dimensions | Width: 45 mm Height: 160 mm |
| Support rails Qty/height | 1 / 7.5 mm |
| To fit manufacturer (model) | ABB Eaton Schneider Electric Siemens MS116 PKZM0 bis 25 A PKZM01 bis 25 A PKE12 PKE32 bis 25 A GV2-P bis 25 A GV2-RT GV2-LE10 GV3 bis 25 A 3RV10 21 3RV20 21 bis 25 A 3RV10 11 3RV20 11 |
| Packs of | 1 pc(s). |
| Net weight | 0.25 kg |

Features

| | |
|------------------------------|--------------------------------------------------------------------------------------------------------------------|
| Gross weight | 0.29 kg |
| Copper weight (kg per piece) | 0.041 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Mini-PLS component adaptor, 25 A, 690 V, 3-pole, connection cable AWG 12, WH: 45x160 mm, support rail H: 7,5 mm |

Approvals

| | |
|--------------|-----------------------------------------------------------|
| Approvals | UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |