

**Rittal – The System.**

Faster – better – everywhere.



**SV 9614.110**

**Mini-PLS component adaptor**

State: 4/05/2025 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9614.110 - Mini-PLS component adaptor

Maximum rated current from 12 A to 100 A.

## Features

Model No.	SV 9614.110
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Connection cables (AWG)	AWG 14
Rated operating voltage	690 V, 3~
Rated current max.	12 A
Dimensions	Width: 45 mm Height: 160 mm
Support rails Qty/height	1 / 7.5 mm
Packs of	1 pc(s).
Net weight	0.23
Gross weight	0.306
Copper weight (kg per piece)	0.038
Customs tariff number	85369095
EAN	4028177240193
ETIM 9	EC001531
ECLASS 8.0	27370304

## Approvals

Approvals	UR + C-UR (recognized)
-----------	------------------------

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK