

# Rittal – The System.

Faster – better – everywhere.



## SZ 1.321.1300.22

## O-Ringe-VMQ

Staat: 22.06.2026 (Bron: [rittal.com/be-nl](http://rittal.com/be-nl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 1.321.1300.22 - O-Ringe-VMQ

## Functies

Bestelnr.	SZ 1.321.1300.22
Uitvoering	O-ring
Materiaal	O-Ringe-VMQ
Binnendiameter	17 mm
Voor PG	13,5
Materiaaldikte	1,5 mm
Bedrijfstemperatuurbereik	-60 °C...250 °C
Leveringseenheid	100 st.
Douanetariefnummer	39269097
Product omschrijving	O-Ring-VMQ, PG, PG 13,5, 17 x 1,8 mm, temp.bereik -60 - 250