

Rittal – The System.

Faster – better – everywhere.



SZ 1.321.2500.59

O-Ringe-VMQ

Staat: 26.04.2026 (Bron: rittal.com/be-nl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1.321.2500.59 - O-Ringe-VMQ

Functies

Bestelnr.	SZ 1.321.2500.59
Uitvoering	O-ring
Materiaal	O-Ringe-VMQ
Binnendiameter	22 mm
Materiaaldikte	2 mm
Bedrijfstemperatuurbereik	-60 °C...250 °C
Leveringseenheid	100 st.
Douanetariefnummer	39269097
Product omschrijving	O-Ring-VMQ, metrisch, M 25 x 1,5, 22 x 2 mm, temp.bereik -60 - 250