

Rittal – The System.

Faster – better – everywhere.



SZ 1.609.4800.61

HSK-M

Staat: 12.12.2025 (Bron: rittal.com/be-nl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1.609.4800.61 - HSK-M

Standaard kabelwartels van messing



Funcities

Bestelnr.	SZ 1.609.4800.61
Uitvoering	recht
Product omschrijving	Standaard kabelwartels van messing
Materiaal	Messing Dichtring: NBR Kleminzetstuk van polyamide
Oppervlak	vernikkeld (mat)
Kleur	Overige
Beschermklasse IP volgens IEC 60529	IP 68 (10 bar) IP 69K
Sleutelwijdte	64 mm
Voor explosie veilige zone gas	Geen
Buigradius (max.)	Nee
Explosie geteste uitvoering	Nee
Halogeenvrij	Ja
Glasvezel versterkt	Nee
Meervoudig dichtingsinzetstuk	Nee
Slagvast	Ja
Met contra moer	Nee

Funcities

Afmetingen	Schroefdraadlengte: 15 mm
Bedrijfstemperatuurbereik	-40 °C...100 °C
Schroefdraadlengte	15 mm
Leveringseenheid	5 st.
Douanetariefnummer	85389099
EAN	4033878430057
ECLASS 8.0	27149109