


Rittal – The System.

Faster – better – everywhere.



KL 1501.510

Terminal boxes KL

State: 26.01.2026 (Source: rittal.com/bg-bg)



FRIEDHELM LOH GROUP

KL 1501.510 - Terminal boxes KL without gland plate

Spray-finished enclosure with sheet steel cover, without gland plate Protection category IP 66.

Features

| | |
|-----------------------------------|---|
| Model No. | KL 1501.510 |
| Material | Enclosure: Sheet steel Cover: Sheet steel, all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure with cover Quick-release fastener including plastic bushes |
| Protection category NEMA | NEMA 4 |
| Protection category to IEC 60 529 | IP 66 |
| IK Code | IK08 |
| Dimensions | Width: 300 mm Height: 150 mm Depth: 120 mm |
| Material thickness - cover | 1,25 mm |
| Material thickness - enclosure | 1,25 mm |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 2.23 |
| Gross weight | 2.38 |
| Customs tariff number | 73269098 |
| EAN | 4028177251137 |
| E-Number Sweden | E3404663 |
| ETIM 9 | EC000261 |

Features

ETIM 8 EC000261

ECLASS 8.0 27180101

Approvals

| | |
|--------------|---|
| Approvals | Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Manufacturer's declaration Declaration of conformity UK |

Tender text

Terminal box without gland plate (120 mm deep),
protection category IP 66

Enclosure:

Robust steel sheet construction, body made from a single folded and welded piece with protection channel around the cover opening; rear panel with counter-sunk holes for wall mounting brackets; steel sheet cover, flush-mounted with highly elastic, foamed-in special seal, with PE conductor connections in the cover and enclosure; with transverse strips fitted on both sides, mounting holes, special plastic bushes for captive cover screws and also used as screwdriver guides.

Accessories:

Enclosure quick-release fastener, cover retainer, plastic cable gland plate, cover hinges, mounting plate

Surface finish:

Panels cleaned, degreased, phosphated, electrophoretic dipcoat primed and powder-coated with polyester powder in textured RAL 7035.

Dimensions (W x H x D): 300 x 150 x 120 mm