

Rittal – The System.

Faster – better – everywhere.



EL 2092.300 Captive nuts

State: 02.08.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



EL 2092.300 - Captive nuts

M5/M6, for the attachment of rack-mounted electronic equipment, 482.6 mm (19") installed equipment and blanking plates to mounting angles, 482.6 mm (19").

Features

| | |
|--------------------------|--|
| Model No. | EL 2092.300 |
| Design | without contact |
| Product description | For the attachment of rack-mounted electronic equipment, 482.6 mm (19") installed equipment and blanking plates to mounting angles, 482.6 mm (19"). For use with metal thickness from 0.8 – 2.5 mm. Optionally with or without contact of the installed equipment to the 482.6 mm (19") section/enclosure. |
| Dimensions | Thread: M6 |
| For material thicknesses | 1.2 - 1.5 mm |
| Packs of | 50 pc(s). |
| Net weight | 0.15 |
| Gross weight | 0.202 |
| Customs tariff number | 73181692 |
| EAN | 4028177187382 |
| ETIM 9 | EC002358 |
| ETIM 8 | EC002358 |
| ECLASS 8.0 | 23110815 |