

Rittal – The System.

Faster – better – everywhere.



EL 2094.300 Captive nuts

State: 05.06.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



EL 2094.300 - Captive nuts

Captive nut, with M6 thread, with contact

Features

| | |
|--------------------------|--|
| Model No. | EL 2094.300 |
| Design | with contact |
| Product description | For the attachment of rack-mounted electronic equipment, 482.6 mm (19") installed equipment and blanking plates to mounting angles, 482.6 mm (19"). For use with metal thickness from 0.8 – 2.5 mm. Optionally with or without contact of the installed equipment to the 482.6 mm (19") section/enclosure. |
| Dimensions | Thread: M6 |
| For material thicknesses | 1.2 - 1.5 mm |
| Packs of | 50 pc(s). |
| Net weight | 0,15 kg |
| Gross weight | 0,23 kg |
| Customs tariff number | 73181692 |
| ETIM 9 | EC002358 |
| ETIM 8 | EC002358 |
| ECLASS 8.0 | 23110815 |
| Product description | EL Captive nuts, M6, With contact, For metal thickness: 1,2-1,5 mm |