

Rittal – The System.

Faster – better – everywhere.



SR 2340.700

Swing frame, large, without trim panel

State: 28.08.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SR 2340.700 - Swing frame, large, without trim panel for TS, VX SE, 600 mm and 1200 mm wide enclosures

For 600 mm and 1200 mm wide enclosures, 22 - 45 U, without trim panel, for mounting 482.6 mm (19") equipment.



Features

| | |
|-----------------------|--|
| Model No. | SR 2340.700 |
| Product description | For mounting 482.6 mm (19") equipment. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Cam with double-bit lock insert Parts for attaching to the installation kit |
| Assembly instruction | Depending on the mounting situation, TS punched sections with mounting flanges 23 x 73 mm or 17 x 73 mm are required |
| Note | For further installation options, see "Technical details" |
| To fit | Enclosure type: TS Width: = 600 mm = 1,200 mm Height: ≥ 2,000 mm |
| Units | 40 U |
| To fit enclosure type | TS |
| Packs of | 1 pc(s). |
| Net weight | 12.271 |

Features

| | |
|-----------------------|---------------|
| Gross weight | 12.917 |
| Customs tariff number | 94039910 |
| EAN | 4028177021679 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189261 |